



CONDAIR CP3

Electrode boiler steam humidifier
Reliable and economic steam humidification



Benefits

- Economic steam humidification
- Reliable operation
- Simple to install & easy to use
- Provides pure, sterile steam
- Long cylinder life

Easy to remove electrode plugs

Cleanable or disposable steam cylinder with zinc coated steel elements. Optional soft water cylinders down to 40µS



Pumped drain increases scale removal and removes waste water rapidly to maintain control accuracy

Large, clear LCD display

Easy to operate keypad

LED operational indicators

Powder coated steel casing as standard (optional stainless steel)



Condair CP3

Electrode boiler steam humidifier



Consistent separation of power and water sections ensures operating safety

e-LINKS for optional BMS connection

Hinged control panel provides easy access to electronics



The Condair CP3 electrode boiler steam humidifier is an economic yet dependable solution for steam humidification.

It is easy to install, simple to use and provides accurate and responsive humidity control. Innovative features such as water conductivity monitoring and staged electrode use maximise the lifetime of the steam cylinder and

extend the operational periods between service requirements.

When servicing is needed, the Condair CP3's design makes it easy to drain, remove and replace the disposable steam cylinder, keeping downtime to a minimum.



The Condair CP3 automatically calculates the conductivity of the water in the boiling cylinder **to provide accurate humidity control.**

Intelligent Water Quality and Level Control

Water conductivity management

An electrode boiler humidifier operates by passing electrical current through water to heat it. As the water evaporates its mineral content becomes more concentrated. This increased level of conductivity affects the level of steam production.

To maintain an accurate output the concentration of minerals in the water is automatically reduced through drainage and replacement with fresh water.

Steel electrodes with “lattice” design


The robust zinc coated steel elements provide a long operational life. Their special lattice structure offers the greatest possible surface area for optimal transfer of current to the water.

Staged electrode use to prolong life

Only the lower sections of the electrodes are initially submerged and used to create steam. During operation the parts of the electrodes submerged in the water become encrusted with

scale. As their conductivity reduces the water level is automatically raised to submerge fresh unused electrodes.

This staged approach to water level control inside the cylinder prolongs the life of the electrodes and helps maintain their efficiency in providing accurate humidity control.





Flexible use, reliable performance and easy product selection - **these are the strengths of the CP3 steam humidifier**

Cleanable or Disposable Steam Cylinders

The steam cylinders are at the heart of Condair CP3 system. During the evaporation process minerals will accumulate in the steam cylinder that after prolonged use will need to be removed.

Depending on your level of desired maintenance, the Condair CP3 offers two options:



Cleanable steam cylinders that can be emptied of scale and reused many times



Disposable steam cylinders to reduce maintenance time and keep the system operating



Modern building management based on integrated technology. Using e-LINKS communication with the humidification system **is simple, quick and clear.**

Easy-to-use with Optional Connection to BMS

Control panel

Operating the Condair CP3 is child's play. The multiple line LCD display indicates all operating parameters, service requirements and fault diagnostics. Control input is via the integrated keypad. The user-friendly software guides you reliably through the menu, even if you infrequently use the unit.


A CP3 card stores all commissioning settings and allows for easy re-commissioning as well as commissioning of several units to the same configuration.

BMS connectivity

The humidifier has an option to be operated from a BMS and accepts Modbus Standard, BACnet or LonWorks protocols.



e-LINKS.




Condair's comprehensive range of steam distribution systems
for any project requirement

Steam Distribution is the Key to Success

Steam distribution must be tailored to the requirements of each project. Whether high or low steam outputs, close humidity control or short duct sections - for every application there is an ideal solution.



Condair steam distribution lances for normal humidification requirements



Condair OptiSorp steam distribution system for short evaporation distance



Condair fan unit for direct room steam humidification

Standard Version


- Disposable steam cylinder
- Internal PI humidity controller
- Control panel with touch pad keyboard and 5-line LCD display
- Self-diagnostic system
- Hours run timer

Options


- All-weather protective housing
- Steam distribution system Condair OptiSorp
- Pressure equalization to 10,000 Pa
- e-NKS (BACnet / LonWorks) for BMS connection
- Humidity sensors and humidistats

Accessories




- 1 Steam distribution
- 2 Steam hose
- 3 Condensate hose
- 4 Water filter isolation valve
- 5 Direct room steam distribution system



Specifications



Condair CP3		5	8	15	20	33	45	52	60	70
Heating voltage		Maximum steam output in kg/h								
400 VAC / 3Ph / 50..60 Hz	kg/h	5	8	15	20	33	45	52	105	152
230 VAC / 3Ph / 50..60 Hz	kg/h	5	8							
Dimensions (WxHxD)	mm	1x 456x620x280			1x 559x667x350			2x 559x667x350		
Control voltage		230 VAC / 1 Ph / 50..60 Hz								
Operating weight (per unit)	kg	1x 26			1x 65			2x 65		
Conformity		CE, GOST, VDE								



Condair CP3		80	90	105	120	135	152	160	180	
Heating voltage		Maximum steam output in kg/h								
400 VAC / 3Ph / 50..60 Hz	kg/h	80	90	105	120	135	152	160	180	
Dimensions (WxHxD)	mm	2x 559x667x350			3x 559x667x350			4x 559x667x350		
Control voltage		230 VAC / 1 Ph / 50..60 Hz								
Operating weight (per unit)	kg	2x 65			3x 65			4x 65		
Conformity		CE, VDE, GOST								